



MASTER LEDspot LV AR111

MAS LEDspotLV D 11-50W 930 AR111 40D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

产品数据

基本資訊	
接口	G53 [G53]
標稱使用時間 (標稱)	40000 h
開關週期	50000X
技術類型	11-50W
照明科技	
色碼	930 [CCT of 3000K]
Beam Angle (Nom)	40°
光分佈	40D [中等光束]
光通量 (標稱)	640 lm
光通量 (額定) (標稱)	640 lm
光強 (標稱)	1150 cd
色彩名稱	白色 (WH)


額定光束角	40°
相關色溫 (標稱)	3000 K
光效 (額定) (標稱)	58.18 lm/W
色彩一致性	<6
演色性指數 (標稱)	90
標稱使用時間結束時的燈具流明維護係數 (標稱)	70 %
Luminous Flux in 90° Cone (Rated)	570 lm
運作和電氣	
Power (Rated) (Nom)	11 W
燈具電流 (標稱)	1300 mA
相等瓦數	50 W
起始時間 (標稱)	0.5 s
至 60% 亮度的暖機時間 (標稱)	instant full light

MASTER LEDspot LV AR111

功率因数 (標稱)	0.7
電壓 (標稱)	12 V
溫度	
T 盒上限 (標稱)	70 °C
控制調光	
可調光	Yes
應用	
能源效益標籤 (EEL)	A
適合重點照明	Yes
能源消耗 kWh/1000 h	13 kWh

產品參數	
完整產品碼	871869651514300
訂購產品名稱	MAS LEDspotLV D 11-50W 930 AR111 40D
EAN/UPC - 產品	8718696515143
訂購代碼	929001170108
分子 - 各件數量	1
分子 - 每一外盒內件數	6
材質編號(12NC)	929001170108
淨重 (件)	0.360 kg



二维绘图



LED D 11-50W 930 AR111 40D

Product	D	C
MAS LEDspotLV D 11-50W 930 AR111 40D	111 mm	62 mm


光度数据



MASTER LEDspot LV AR111 50W G53 930 40D


MASTER LEDspot LV AR111

光度数据




SDPO_LEDspotL_0026-Spectral Power distribution

壽命



MASTER LEDspotLV AR111 75W G53 940 40D



MASTER LEDspotLV AR111 75W G53 940 40D

