



MASTER LEDspot LV AR111

MAS LEDspotLV D 15-75W 927 AR111 24D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

产品数据


基本資訊		色彩一致性	
接口	G53 [G53]	演色性指數 (標稱)	<6
標稱使用時間 (標稱)	40000 h	標稱使用時間結束時的燈具流明維持係數 (標稱)	90
開關週期	50000X	Luminous Flux in 90° Cone (Rated)	70 %
技術類型	15-75W		760 lm
照明科技		運作和電氣	
色碼	927	Power (Rated) (Nom)	15 W
Beam Angle (Nom)	24 °	燈具電流 (標稱)	1800 mA
光通量 (標稱)	830 lm	相等瓦數	75 W
光強 (標稱)	3900 cd	起始時間 (標稱)	0.5 s
色彩名稱	暖 白色 (WW)	至 60% 亮度的暖機時間 (標稱)	instant full light
相關色溫 (標稱)	2700 K	功率因數 (標稱)	0.7
光效 (額定) (標稱)	55.33 lm/W	電壓 (標稱)	12 V

MASTER LEDspot LV AR111

溫度	
T 盒上限 (標稱)	74 °C
控制調光	
可調光	Yes
應用	
能源效益標籤 (EEL)	A
適合重點照明	Yes
能源消耗 kWh/1000 h	16 kWh

產品參數	
完整產品碼	871869651516700
訂購產品名稱	MAS LEDspotLV D 15-75W 927 AR111 24D
EAN/UPC - 產品	8718696515167
訂購代碼	929001170208
分子 - 各件數量	1
分子 - 每一外盒內件數	6
材質編號(12NC)	929001170208
淨重 (件)	0.360 kg


二维绘图




LED D 15-75W 927 AR111 24D

Product	D	C
MAS LEDspotLV D 15-75W 927 AR111 24D	111 mm	62 mm

光度数据



MASTER LEDspot LV AR111 75W G53 927 24D




MASTER LEDspot LV AR111

光度数据




SDPO_LEDspotL_0027-Spectral Power distribution

壽命



MASTER LEDspotLV AR111 75W G53 940 40D



MASTER LEDspotLV AR111 75W G53 940 40D

