

MAS LEDspotLV D 15-75W 930 AR111 40D

MASTER LEDspot LV AR111

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- **Dimmable:** Yes
- **Energy Efficiency Label:** A
- **Luminous Efficacy (rated) (Nom):** 54.00 lm/W
- **Power (Rated) (Nom):** 15 W

Circularity

- **Nominal Lifetime (Nom):** 40000 h

Packaging

- **SAP Weight Paper Unit (Case):** 0.630 kg
- **SAP Weight Paper Unit (Piece):** 0.050 kg

Substances

- **EU REACH SVHC declaration:** Yes
- **EU RoHS compliant:** No
- **Halogen free compliant:** No

Weight & Materials

- **Net Weight (Piece):** 0.160 kg