



MASTER LEDspot LV AR111

MAS LEDspotLV D 20-100W 830 AR111 12D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

产品数据

基本資訊	
接口	G53 [G53]
標稱使用時間 (標稱)	25000 h
開關週期	50000X
技術類型	20-100W

照明科技	
色碼	830 [CCT of 3000K]
Beam Angle (Nom)	12°
光分佈	12D [窄光束]
光通量 (標稱)	1350 lm
光通量 (額定) (標稱)	1350 lm
光強 (標稱)	10000 cd
色彩名稱	白色 (WH)

額定光束角	12°
相關色溫 (標稱)	3000 K
光效 (額定) (標稱)	67.50 lm/W
色彩一致性	<6
演色性指數 (標稱)	80
標稱使用時間結束時的燈具流明維護係數 (標稱)	70 %

運作和電氣	
Power (Rated) (Nom)	20 W
燈具電流 (標稱)	2400 mA
相等瓦數	100 W
起始時間 (標稱)	0.5 s
至 60% 亮度的暖機時間 (標稱)	instant full light
功率因數 (標稱)	0.7


MASTER LEDspot LV AR111

電壓 (標稱)	12 V
溫度	
T 盒上限 (標稱)	80 °C
控制調光	
可調光	Yes
應用	
適合重點照明	Yes
能源消耗 kWh/1000 h	22 kWh

產品參數

完整產品碼	871869651524200
訂購產品名稱	MAS LEDspotLV D 20-100W 830 AR111 12D
EAN/UPC - 產品	8718696515242
訂購代碼	929001170608
分子 - 各件數量	1
分子 - 每一外盒內件數	6
材質編號(12NC)	929001170608
淨重 (件)	0.360 kg



二维绘图



LED D 20-100W 830 AR111 12D

Product	D	C
MAS LEDspotLV D 20-100W 830 AR111 12D	111 mm	62.3 mm

光度数据



MASTER LEDspot LV AR111

