



MASTER LEDspot LV AR111

MAS LEDspotLV D 20-100W 840 AR111 40D

Delivering a warm, halogen-like accent beam, MASTER LEDspot LV AR111 is an ideal retrofit solution for spot and general lighting applications in the hospitality and retail industry. It is particularly suitable for general lighting where the light is on all the time, such as creative accent lighting applications in shops, restaurants, hotels, and especially for galleries, exhibitions and museums. The robustly designed MASTER LEDspot LV AR111 offers various beam angles for a clearly defined beam spread. There is no UV or IR in the beam, making it suitable for illuminating heat-sensitive objects (food, organic materials, paintings, etc.). The patented intelligent driver enables broad compatibility with existing electromagnetic and electronic halogen transformers. MASTER LEDspot LV AR111 delivers huge energy savings and minimizes maintenance cost without any reduction in brightness.

产品数据

基本資訊	
接口	G53 [G53]
符合歐盟 RoHS 標準	是
標稱使用時間 (標稱)	25000 h
開關週期	50000X
技術類型	20-100W
照明科技	
色碼	840 [CCT of 4000K (841)]
Beam Angle (Nom)	40 °
光通量 (標稱)	1400 lm
光強 (標稱)	2350 cd
色彩名稱	冷 白色 (CW)
相關色溫 (標稱)	4000 K


光效 (額定) (標稱)	70 lm/W
色彩一致性	<6
演色性指數 (標稱)	80
標稱使用時間結束時的燈具流明維護係數 (標稱)	70 %
運作和電氣	
輸入頻率	- Hz
Power (Rated) (Nom)	20 W
燈具電流 (標稱)	2400 mA
相等瓦數	100 W
起始時間 (標稱)	0.5 s
至 60% 亮度的暖機時間 (標稱)	instant full light
功率因數 (標稱)	0.7

MASTER LEDspot LV AR111

電壓 (標稱)	12 V
溫度	
T 盒上限 (標稱)	80 °C
控制調光	
可調光	是
應用	
能源效益標籤 (EEL)	Not applicable
適合重點照明	Yes
能源消耗 kWh/1000 h	22 kWh

產品參數	
完整產品碼	871869651530300
訂購產品名稱	MAS LEDspotLV D 20-100W 840 AR111 40D
EAN/UPC - 產品	8718696515303
訂購代碼	929001171308
分子 - 各件數量	1
分子 - 每一外盒內件數	6
材質編號(12NC)	929001171308
淨重 (件)	0.360 kg


二维绘图




LED D 20-100W 840 AR111 40D

Product
MAS LEDspotLV D 20-100W 840 AR111 40D

光度数据




MASTER LEDspot LV AR111 100W G53 840 40D





MASTER LEDspot LV AR111

光度数据



壽命



MASTER LEDspotLV AR111 100W G53 40D

MASTER LEDspotLV AR111 100W G53 40D

