



# MASTER LEDtube EM/ Mains T8

## MAS LEDtube 600mm 10W830 T8 I

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. This product is the ideal solution for up lighting in general lighting applications.

### Warnings and Safety

- -
- -

### Product data


General Information		Operating and Electrical	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	Line Frequency	50 to 60 Hz
Nominal lifetime	40,000 hour(s)	Input Frequency	50 to 60 Hz
Switching Cycle	50,000	Power Consumption	10 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.9
Color Code	830 [CCT of 3000K]	Voltage (Nom)	220-240 V
Beam Angle (Nom)	160 degree(s)	Temperature	
Luminous Flux	1,000 lm	Ambient temperature range	-20 °C to 45 °C
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	60 °C
Color Consistency	<6	Controls and Dimming	
Color rendering index (CRI)	83	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %		

# MASTER LEDtube EM/Mains T8

Mechanical and Housing	
Product Length	600 mm
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Approval Marks	RoHS compliance KEMA Keur certificate CE marking
Energy Consumption kWh/1000 h	10 kWh
Product Data	
Order product name	MAS LEDtube 600mm 10W830 T8 I

Full product name	MAS LEDtube 600mm 10W830 T8 I
Full product code	871869651122000
Order code	929001178808
Material Nr. (12NC)	929001178808
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696511220
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696511237

## Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 600mm 10W830 T8 I	25.7 mm	28 mm	588.5 mm	595.5 mm	602.5 mm

