



# Premium LED bulbs - Dimmable and features

## BC9.5A19/AMB/822-827 DIM 120V LA

Create a warm, inviting ambiance with the Philips dimmable Premium LED bulbs. The Philips LED WarmGlow bulbs offer a new experience for dimmable LEDs, by enabling light levels to dim to the warm tones of traditional lamps. You can change the ambiance from functional lighting to an inviting and cozy atmosphere.

### Product data

General Information	
Cap-Base	E26 [ Single Contact Medium Screw]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	9.5-60W
Light Technical	
Color Code	822-827 [ tunable warm white]
Beam Angle (Nom)	250 °
Luminous Flux (Nom)	800 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2200-2700 K
Luminous Efficacy (rated) (Nom)	84.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power (Nom)	9.5 W
Lamp Current (Nom)	100 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	100 °C
Controls and Dimming	
Dimmable	Yes

## Premium LED bulbs - Dimmable and features

### Mechanical and Housing

Bulb Finish Frosted

### Approval and Application

Energy Consumption kWh/1000 h 9.5 kWh

### Product Data

Full product code 871869681785800  
Order product name BC9.5A19/AMB/822-827 DIM 120V LA

EAN/UPC - Product 8718696817858

Order code 929001184011


Numerator - Quantity Per Pack 1

Numerator - Packs per outer box 6

Material Nr. (12NC) 929001184011

Net Weight (Piece) 0.060 kg


### Dimensional drawing




Bulb A19 120V 9.5W-60W 800lm 2700K E26 D

Product	D	C
BC9.5A19/AMB/822-827 DIM 120V LA	61.4 mm	109.8 mm

### Photometric data




LEDlamps, A19 E26 2700 800lm



LEDlamps, A19 9.5W-60W 2200-2700K 800lm

## Premium LED bulbs - Dimmable and features

### Photometric data



LEDlamps, A19 9.5W-60W 2200-2700K 800lm

