



Ecofit Ledtubes T8

LEDtube 1200mm 16W 740 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data


General Information		Power Factor (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]		0.5
Main Application	Industrial	Voltage (Nom)	220-240 V
Nominal Lifetime (Nom)	15000 h	Temperature	
Switching Cycle	50000X	T-Ambient (Max)	45 °C
B50L70	15000 h	T-Ambient (Min)	-20 °C
Light Technical		T-Storage (Max)	65 °C
Color Code	740 [CCT of 4000K]	T-Storage (Min)	-40 °C
Luminous Flux (Nom)	1600 lm	T-Case Maximum (Nom)	60 °C
Luminous Flux (Rated) (Nom)	1600 lm	Controls and Dimming	
Correlated Color Temperature (Nom)	4000 K	Dimmable	No
Color Consistency	<7	Mechanical and Housing	
Color Rendering Index (Nom)	73	Product Length	1200 mm
LLMF At End Of Nominal Lifetime (Nom)	70 %	Approval and Application	
Operating and Electrical		Energy Efficiency Label (EEL)	A+
Input Frequency	50 to 60 Hz	Energy Saving Product	Yes
Power (Rated) (Nom)	16 W	Suitable For Accent Lighting	No
Lamp Current (Nom)	120 mA	Approval Marks	RoHS compliance KEMA Keur certificate
Starting Time (Nom)	0.5 s		
Warm Up Time to 60% Light (Nom)	0.5 s		

Ecofit Ledtubes T8

Energy Consumption kWh/1000 h	16 kWh
Product Data	
Full product code	871869652501200
Order product name	LEDtube 1200mm 16W 740 T8 AP C G
EAN/UPC - Product	8718696525012
Order code	929001184508

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001184508
Net Weight (Piece)	0.210 kg



Dimensional drawing




TLED 1200mm 4ft T8 16W-36W 4000K G13 ND

Product	D1	D2	A1	A2	A3	C	D
LEDtube 1200mm	25.68	28 mm	1198	1205	1212	1212	27.8
16W 740 T8 AP C G	mm		mm	mm	mm	mm	mm

Photometric data



LEDtube 1200mm 16W 740 T8 CN I G





Ecofit Ledtubes T8

Lifetime




LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

LEDtube 16W G13 740 T8 AP I G



LEDtube 16W G13 740 T8 AP I G

Ecofit Ledtubes T8

