



# Ecofit Ledtubes T8

## LEDtube 600mm 8W 740 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

### Product data


General Information		Power factor (nom.)	
Cap base	G13 [ Medium Bi-Pin Fluorescent]		0.5
Main application	Industrial	Voltage (Nom)	220–240 V
Nominal lifetime (nom.)	15000 h	<b>Temperature</b>	
Switching cycle	50000X	T ambient (max.)	45 °C
B50L70	15000 h	T ambient (min.)	-20 °C
<b>Light Technical</b>		T storage (max.)	65 °C
Colour Code	740 [ CCT of 4,000 K]	T storage (min.)	-40 °C
Lamp Luminous Flux 25°C EL (Nom)	800 lm	T-Case maximum (nom.)	60 °C
Lamp Luminous Flux (Nom)	800 lm	<b>Controls and Dimming</b>	
Colour Temperature, horizontal (Nom)	4000 K	Dimmable	no
Colour consistency	<7	<b>Mechanical and Housing</b>	
Colour Rendering Index, horiz (Nom)	73	Product length	600 mm
LLMF at end of nominal lifetime (nom.)	70 %	<b>Approval and Application</b>	
<b>Operating and Electrical</b>		Energy efficiency label (EEL)	A+
Input frequency	50 to 60 Hz	Energy-saving product	Yes
Power (Rated) (Nom)	8 W	Suitable for accent lighting	No
Lamp current (nom.)	70 mA	Approval marks	RoHS compliance KEMA Keur certificate
Starting time (nom.)	0.5 s		
Warm-up time to 60% light (nom.)	0.5 s		

# Ecofit Ledtubes T8

Energy Consumption kWh/1000 h	8 kWh
<b>Product Data</b>	
Full product code	871869652505000
Order product name	LEDtube 600mm 8W 740 T8 AP C G
EAN/UPC – product	8718696525050
Order code	929001184708

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001184708
Net weight (piece)	0.124 kg



## Dimensional drawing



TLED 600mm 2ft T8 8W-18W 4000K G13 ND


Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28	588.5	595.5	602.5	602.5	27.8
8W 740 T8 AP C	mm	mm	mm	mm	mm	mm	mm
G							

## Photometric data



LEDtube 600mm 8W 740 T8 CN I G

LEDtube 600mm 8W 765 T8 CN I G



LEDtube 600mm 8W G13 T8 740 800lm AP C G

# Ecofit Ledtubes T8

## Lifetime

