

Ecofit LED tubes T8 Mains

LEDtube 600mm 8W 740 T8 AP C G

Upgrade to efficient, long-lasting LED tubes with the Ecofit LED tubes. Ecofit LED tubes are a fast and easy way to replace your old fluorescent tubes with modern, efficient LED technology. Good quality of light with a natural lighting effect for use in general lighting applications with low initial investment – an environmentally friendly solution.

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
Main application	Industrial
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
B50L70	15000 h
Light Technical	
Colour Code	740 [CCT of 4000K]
Lamp Luminous Flux 25°C EL (Nom)	800 lm
Lamp Luminous Flux (Nom)	800 lm
Colour Temperature, horizontal (Nom)	4000 K
Colour consistency	<7
Colour Rendering Index,horiz (Nom)	73
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Technical Lamp Power (Nom)	8 W
Lamp current (nom.)	70 mA

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (nom.)	220-240 V
Temperature	
T ambient (max.)	45 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	60 °C
Controls and Dimming	
Dimmable	no
Mechanical and Housing	
Product length	600 mm
Approval and Application	
Energy-saving product	Yes

Ecofit LED tubes T8 Mains


Suitable for accent lighting	No
Energy efficiency label (EEL)	A+
Approval marks	RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	8 kWh

Product Data

Full product code	871869652505000
Order product name	LEDtube 600mm 8W 740 T8 AP C G

EAN/UPC – product	8718696525050
Order code	929001184708
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001184708
Net weight (piece)	0.124 kg




Dimensional drawing



TLED 600mm 2ft T8 8W-18W 4000K G13 ND

Product	D1	D2	A1	A2	A3	C	D
LEDtube 600mm	25.68	28 mm	588.5	595.5	602.5	602.5	27.8
8W 740 T8 AP C G	mm		mm	mm	mm	mm	mm
G							

Photometric data



Ecofit LED tubes T8 Mains

Lifetime

