



BR/R LED

10BR40/LED/850/DIM 120V 6/1

Philips Dimmable LED Reflector Lamps provide a soft, diffused level of light and smooth dimming to reduce glare. The sleek, lightweight design is ideal for downlighting.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
RoHS mark	RoHS mark
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	10-60 W

Light Technical	
Color Code	850 [CCT of 5000K]
Initial lumen (Nom)	800 lm
Luminous Flux (Rated) (Nom)	800 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	80 lm/W
Color Consistency	<7
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	10 W
Lamp Current (Nom)	120 mA
Wattage Equivalent	65 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	85 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Frosted (FR)


Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	8 kWh

Product Data	
Order product name	10BR40/LED/850/DIM 120V
EAN/UPC - Product	046677459833
Order code	459834
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001195004

BR/R LED

Net Weight (Piece) 0.165 kg



Dimensional drawing



BR40 120V 8.5-65W 650lm 110D 5000K E26 D

Product	D	C
10BR40/LED/850/DIM 120V	127 mm	162 mm

Photometric data



LEDbulb, Basic BR40 8-65W 5000K 650lm

