



CorePro LED PLC

CorePro LED PLC 9W 830 4P G24q-3

Philips CorePro LED PLC is the ideal uplamping solution for downlights in a wide range of general lighting applications. It integrates a LED light source into a traditional fluorescent form factor to offer superb energy savings over a lifetime that's twice as long as fluorescent alternatives.

Product data

General Information	
Cap base	G24Q-3 [G24q-3]
Nominal lifetime (nom.)	30000 h
Switching cycle	50000X
B50L70	30000 h
Light Technical	
Colour code	830 [CCT of 3,000 K]
Luminous flux (nom.)	950 lm
Luminous flux (rated) (nom.)	950 lm
Correlated colour temperature (nom.)	3000 K
Colour consistency	<6
Color rendering index (nom.)	83
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	30000-80000 Hz
Power (Rated) (Nom)	9 W
Lamp current (max.)	400 mA
Lamp current (min.)	250 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9

Voltage (Nom)	20-50 V
Temperature	
T ambient (max.)	35 °C
T ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	76 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product length	200 mm
Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	12 kWh


CorePro LED PLC

Product Data

Full product code	871869654115900
Order product name	CorePro LED PLC 9W 830 4P G24q-3
EAN/UPC – product	8718696541159
Order code	54115900
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001200802
Net weight (piece)	0.088 kg


Dimensional drawing



LEDtube PLC 9W G24q-3/830 4P



Product	D1	D2	A1	A2	A3
CorePro LED PLC 9W 830 4P G24q-3	24.3 mm	28.4 mm	128.8 mm	148 mm	163.6 mm

Photometric data



General Information 11 Photo Lighting 11 Page 117

LEDtube PLC 100mm 9W G24Q-3 830 950lm




CorePro LED PLC


Lifetime




LEDtube PLC 100mm 9W G24Q-3 830 950lm




LEDtube PLC 100mm 9W G24Q-3 830 950lm



LEDtube PLC 100mm 9W G24Q-3 830 950lm



LEDtube PLC 100mm 9W G24Q-3 830 950lm



LEDtube PLC 100mm 9W G24Q-3 830 950lm

CorePro LED PLC

