



CorePro LED PLC 2P

LED PLC 8.5W 830 2P G24d-3

CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data

General Information	
Cap-Base	G24d-3
Nominal lifetime	30,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	950 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	111.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	83
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	8.5 W
Lamp Current (Max)	43 mA


Lamp Current (Min)	33 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 °C to 35 °C
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	200 mm
Bulb Shape	PL-C
Approval and Application	
Energy Saving Product	Yes
Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate
Energy Consumption kWh/1000 h	11 kWh

CorePro LED PLC 2P

Product Data	
Order product name	LED PLC 8.5W 830 2P G24d-3
Full product name	LED PLC 8.5W 830 2P G24d-3
Full product code	871869666999000
Local code description	LEDPL8.5W8302P
Order code	929001201208
Material Nr. (12NC)	929001201208



Local order code	LEDPL8.5W8302P
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696669990
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696670002

Dimensional drawing




Product	D1	D2	A1	A2	A3
LED PLC 8.5W 830 2P G24d-3	24.3 mm	28.4 mm	128.8 mm	148 mm	170.6 mm

Photometric data



General uniform lighting - LED PLC 8.5W 830 2P G24d-3



Light Distribution Diagram - LED PLC 8.5W 830 2P G24d-3




Spectral Power Distribution Colour - LED PLC 8.5W 830 2P G24d-3

CorePro LED PLC 2P


Lifetime




Life Expectancy Diagram - LED PLC 8.5W 830 2P G24d-3



Life Expectancy Diagram - LED PLC 8.5W 830 2P G24d-3



Life Expectancy Diagram - LED PLC 8.5W 830 2P G24d-3



Lumen Maintenance Diagram - LED PLC 8.5W 830 2P G24d-3

Lumen Maintenance Diagram - LED PLC 8.5W 830 2P G24d-3

CorePro LED PLC 2P

