



CorePro LED PLC 2P

LED PLC 6.5W 830 2P G24d-2

CorePro LED PLC 2P integrates a LED light source into a traditional fluorescent form factor. This product is the ideal solution for uplampping in general lighting applications: it meets basic lighting requirements, offers significant energy savings, and is environmentally friendly.

Product data

General information		Warm Up Time to 60% Light (Nom)	
Cap-Base	G24D-2 [G24d-2]		0.5 s
EU RoHS compliant	Yes	Power Factor (Nom)	0.9
Nominal Lifetime (Nom)	30000 h	Voltage (Nom)	220-240 V
Switching Cycle	50000		
Light technical		Temperature	
Color Code	830 [CCT of 3000K]	T-Ambient (Max)	35 °C
Beam Angle (Nom)	120 °	T-Ambient (Min)	-20 °C
Luminous Flux (Nom)	650 lm	T-Storage (Max)	65 °C
Color Designation	White (WH)	T-Storage (Min)	-40 °C
Correlated Color Temperature (Nom)	3000 K	T-Case Maximum (Nom)	65 °C
Luminous Efficacy (rated) (Nom)	100.00 lm/W		
Color Consistency	<6	Controls and dimming	
Color Rendering Index (Nom)	83	Dimmable	No
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and electrical		Mechanical and housing	
Input Frequency	50 to 60 Hz	Product Length	100 mm
Power (Nom)	6.5 W	Bulb Shape	Tube, single-ended
Lamp Current (Max)	35 mA		
Lamp Current (Min)	25 mA	Approval and application	
Starting Time (Nom)	0.5 s	Energy Saving Product	Yes
		Approval Marks	TUV CE marking RoHS compliance KEMA Keur certificate

CorePro LED PLC 2P

Energy Consumption kWh/1000 h	9 kWh
Product data	
Full product code	871869667003300
Order product name	LED PLC 6.5W 830 2P G24d-2
EAN/UPC - Product	8718696670033
Order code	929001201408

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001201408
Net Weight (Piece)	0.080 kg



Dimensional drawing




Product	D1	D2	A1	A2	A3
LED PLC 6.5W 830 2P G24d-2	24.3 mm	28.4 mm	105.8 mm	125 mm	147.6 mm

LED PLC 6.5W 830 2P G24d-2

Photometric data





LEDtube PLC 100mm 7W G24D-2 830 650lm



CorePro LED PLC 2P

Lifetime



LEDtube PLC 100mm 7W G24D-2 830 650lm

LEDtube PLC 100mm 7W G24D-2 830 650lm



LEDtube PLC 100mm 7W G24D-2 830 650lm

LEDtube PLC 100mm 7W G24D-2 830 650lm



LEDtube PLC 100mm 7W G24D-2 830 650lm

CorePro LED PLC 2P

