



# TrueForce High Lumen PAR

## 32PAR38/LED/830/S15/ND SO 120V 6/1

Philips LED TrueForce PAR high lumen lamps are the perfect transition from CDM lamps to LED.

### Product data

General Information	
Base	E26 [ Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	32-250W

Light Technical	
Color Code	830 [ CCT of 3000K]
Beam Angle (Nom)	15 °
Initial lumen (Nom)	2800 lm
Luminous Flux (Rated) (Nom)	2800 lm
Luminous Intensity (Nom)	30000 cd
Color Designation	White (WH)
Rated Beam Angle	15 °
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	88 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	50 to 60 Hz

Power (Rated) (Nom)	32 W
Lamp Current (Nom)	280 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.85
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	95 °C

Controls and Dimming	
Dimmable	No


Approval and Application	
Energy Efficiency Label (EEL)	Not applicable
Suitable For Accent Lighting	Yes

Product Data	
Order product name	120V PAR38 32W 15D 3000K SO
EAN/UPC - Product	046677460518
Order code	460519
Numerator - Quantity Per Pack	1

# TrueForce High Lumen PAR

Numerator - Packs per outer box	6
Material Nr. (12NC)	929001202304
Net Weight (Piece)	0.540 kg



## Dimensional drawing



PAR38 35W-70W 2800lm 15D 3000K E26 ND


Product	D	C
120V PAR38 32W 15D 3000K SO	122 mm	133 mm

## Photometric data



LEDspot, PAR38 35W 2800lm 3000K

LEDspot, PAR38 35W 2800lm 3000K 15D



## TrueForce High Lumen PAR

