



CorePro LEDcandle

CorePro lustre ND 3.5-25W E14 840 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LED lamps deliver huge energy savings and minimize maintenance cost.

Product data


| General Information | | Warm-up time to 60% light (nom.) | |
|--|---------------------------|------------------------------------|--|
| Cap base | E14 [E14] | | 0.5 s |
| EU RoHS compliant | Yes | Power factor (nom.) | 0.4 |
| Nominal lifetime (nom.) | 15000 h | Voltage (Nom) | 220-240 V |
| Switching cycle | 50,000X | Temperature | |
| Technical type | 3.5-25W | T-Case maximum (nom.) | 75 °C |
| Light Technical | | Controls and Dimming | |
| Colour Code | 841 [CCT of 4100K (841)] | Dimmable | No |
| Luminous flux (nom.) | 290 lm | Mechanical and Housing | |
| Colour designation | Cool White (CW) | Lamp Finish | Frosted |
| Correlated Colour Temperature (Nom) | 4000 K | Bulb shape | P45 [P 45mm] |
| Luminous efficacy (rated) (nom.) | 82.86 lm/W | Approval and Application | |
| Colour consistency | <6 | Energy efficiency label (EEL) | A+ |
| Colour rendering index (nom.) | 80 | Energy consumption kWh/1,000 hours | 4 kWh |
| LLMF at end of nominal lifetime (nom.) | 70 % | Product Data | |
| Operating and Electrical | | Full product code | 871869654352800 |
| Input frequency | 50 to 60 Hz | Order product name | CorePro lustre ND 3.5-25W E14 840 P45 FR |
| Power (Rated) (Nom) | 3.5 W | EAN/UPC – product | 8718696543528 |
| Lamp current (nom.) | 35 mA | Order code | 54352800 |
| Wattage equivalent | 25 W | | |
| Starting time (nom.) | 0.5 s | | |

CorePro LEDcandle

| | |
|-----------------------------------|--------------|
| SAP numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 10 |
| SAP material | 929001205702 |

| | |
|------------------------|----------|
| SAP net weight (piece) | 0.040 kg |
|------------------------|----------|



Dimensional drawing



LED ND 3.5-25W E14 840 P45 FR


| Product | D | C |
|--|-------|-------|
| CorePro lustre ND 3.5-25W E14 840 P45 FR | 45 mm | 88 mm |

Photometric data



CorePro LEDlustre 25W E14 840 FR P45


CorePro LEDlustre 25W E14 840 FR P45



SDPO_LEDLSR_0006-Spectral Power distribution

CorePro LEDcandle

Lifetime



LEDbulb 60W E14 827 FR B38

LEDbulb 60W E14 827 FR B38

