



# CorePro LEDcandle

## CorePro lustre ND 3.5-25W E14 840 P45 FR

The frosted CorePro LEDcandle is designed for retrofit replacement of incandescent lamps. It is compatible with fixtures with an E14 holder and is an attractive product for chandeliers. LEDlamps deliver huge energy savings and minimize maintenance cost.

### Product data


General Information	
Cap-Base	E14 [ E14]
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	3.5-25W
Light Technical	
Colour Code	840 [ CCT of 4000K]
Luminous Flux (Nom)	290 lm
Luminous Flux (Rated) (Nom)	290 lm
Colour Designation	Cool White (CW)
Colour Temperature, horizontal (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	82.86 lm/W
Color Consistency	<6
Colour Rendering Index horiz (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Rated) (Nom)	3.5 W
Lamp Current (Nom)	35 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s

Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	75 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted (FR)
Approval and Application	
Energy Efficiency Label	A+
Energy Consumption kWh/1000 h	4 kWh
Product Data	
Full product code	871869654352800
Order product name	CorePro lustre ND 3.5-25W E14 840 P45 FR
EAN/UPC - Product	8718696543528
Order code	54352800
Numerator - Quantity Per Pack	1

# CorePro LEDcandle

Numerator - Packs per outer box	10
Material Nr. (12NC)	929001205702
Net Weight (Piece)	0.040 kg



## Dimensional drawing



LED ND 3.5-25W E14 840 P45 FR


Product	D	C
CorePro lustre ND 3.5-25W E14 840 P45 FR	45 mm	88 mm

## Photometric data



CorePro LEDlustre 25W E14 840 FR P45

CorePro LEDlustre 25W E14 840 FR P45




ND E14 /840 P45

# CorePro LEDcandle

## Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

