

PHILIPS

Eco passport

BC7MR16/AMB/F35/3000 DIM 12V MR16/GU10/PAR16

Philips MR16 Dimmable LED Lamps provide ambient level light to illuminate hard to maintain applications. Increased transformer compatibility allows for operation on a wider range of transformers. Available in dimmable and non-dimmable versions, these lamps are ideal for track and open recessed fixtures in retail, hospitality and residential spaces.



Our Eco passport

Signify leads the way to brighter lives and a better world. As part of the design process we innovate to reduce environmental impact and bring wider benefits to the world we operate in.

We know this is important to you too. So we have developed an eco passport explaining the environmental and social performance of our products in eight Sustainable Focal Areas, developed through our Sustainable Design process since 1994.

Energy

- **Dimmable:** Yes
- **Luminous Efficacy (rated) (Nom):** 71.43 lm/W
- **Power (Rated) (Nom):** 7 W

Circularity

- **Nominal Lifetime (Nom):** 25000 h

Packaging

- **SAP Weight Paper Unit (Case):** 0.298 kg
- **SAP Weight Paper Unit (Piece):** 0.030 kg
- **SAP Weight Plastic Unit (Case):** 0.133 kg
- **SAP Weight Plastic Unit (Piece):** 0.033 kg

Substances

- **EU RoHS compliant:** No

Weight & Materials

- **Net Weight (Piece):** 0.006 kg

Further reading at:
<https://www.signify.com/global/sustainability/sustainable-lighting>

© 2019 Signify Holding. All rights reserved.