



LED A15

2A15/LEDFilament/822/CL/ND 120V

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.

Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	822 [CCT of 2200K]
Luminous Flux	220 lm
Color Designation	Warm/Extra Warm/Very Warm
Correlated Color Temperature (Nom)	2200 K
Luminous Efficacy (rated) (Nom)	110 lm/W
Color Consistency	ANSI
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	2 W
Lamp Current (Nom)	44 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s

Power Factor (Fraction)	0.4
Voltage (Nom)	110-130 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A15 [A 15mm]
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	2A15/LEDFilament/822/CL/ND 120V
Full product name	2A15/LEDFilament/822/CL/ND 120V
Order code	929001209604
Material Nr. (12NC)	929001209604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677461119
Numerator - Packs per outer box	10



LED A15

EAN/UPC - Case	50046677461114
----------------	----------------

Dimensional drawing


Product	D	C
2A15/LEDFilament/822/CL/ND 120V	47 mm	80 mm

Photometric data



Spectral Power Distribution Colour - 2A15/LEDFilament/822/CL/ND 120V

General uniform lighting - 2A15/LEDFilament/822/CL/ND 120V



Light Distribution Diagram - 2A15/LEDFilament/822/CL/ND 120V

LED A15

