



# LED Designer Deco

## 5.5ST19/LEDFilament/820/CL-A/DIM 120V

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings


### Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux	400 lm
Color Designation	Warm
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	72 lm/W
Color Consistency	ANSI
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	60 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s

Power Factor (Fraction)	0.7
Voltage (Nom)	110-130 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	ST19
Approval and Application	
Energy Consumption kWh/1000 h	- kWh
Product Data	
Order product name	5.5ST19/LEDFilament/820/CL-A/DIM 120V
Full product name	5.5ST19/LEDFilament/820/CL-A/DIM 120V
Order code	461673
Material Nr. (12NC)	929001210204
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677461676
Numerator - Packs per outer box	6


EAN/UPC - Case 50046677461671

Dimensional drawing




Product	D	C
5.5ST19/LEDFilament/820/CL-A/DIM 120V	2-9/16 inch	5-7/16 inch


Photometric data



Spectral Power Distribution Colour - 5.5ST19/LEDFilament/820/CL-A/DIM 120V



General uniform lighting - 5.5ST19/LEDFilament/820/CL-A/DIM 120V



Light Distribution Diagram - 5.5ST19/LEDFilament/820/CL-A/DIM 120V

## LED Designer Deco

