



LED A15

5.5A15/LED/827-22/E26/CL/DIM 120V

Philips A15 LED Lamps offer energy saving ambience with an elegant effect. Their unique design provides light in all directions, giving lighting designers a long life alternative to standard incandescent sources.


Product data

General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
Technical Type	5.5-40W
Light Technical	
Color Code	822-827 [tunable warm white]
Luminous Flux (Nom)	450 lm
Luminous Flux (Rated) (Nom)	450 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200-2700 K
Luminous Efficacy (rated) (Nom)	81.82 lm/W
Color Consistency	ANSI 2700K
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power (Rated) (Nom)	5.5 W
Lamp Current (Nom)	60 mA
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7

Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	CL [Clear (CL)]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Certifications	Energy Star
Product Data	
Order product name	5.5A15/LED/827-22/E26/CL/DIM 120V
EAN/UPC - Product	046677462529
Order code	462523
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001215004
Net Weight (Piece)	0.072 kg

LED A15



Dimensional drawing



SS Clear Bulb A15 CL 6W-40W 450lm 330D E26D

Product	D	C
5.5A15/LED/827-22/E26/CL/DIM 120V	50 mm	93 mm

Photometric data



LED Bulb 6-40W A15 E26 CL

