



Classic LEDspotMV

Essential LED 4.6-50W GU10 827 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.

Product data

General Information	
Cap base	GU10 [GU10]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	4.6-50W
Light Technical	
Colour Code	827 [CCT of 2700K]
Technical Beam Angle (Nom)	36 °
Lamp Luminous Flux 25°C EL (Nom)	395 lm
Lamp Luminous Flux (Nom)	395 lm
Luminous intensity (nom.)	700 cd
Colour Designation	Warm white (WW)
Rated beam angle	36 °
Colour Temperature, horizontal (Nom)	2700 K
Lamp Luminous Efficacy EM (Nom)	85.90 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Technical Lamp Power (Nom)	4.6 W


Lamp current (nom.)	39 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.5
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	78 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Suitable for accent lighting	Yes
Energy efficiency label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Full product code	871869670059400
Order product name	Essential LED 4.6-50W GU10 827 36D
EAN/UPC – product	8718696700594
Order code	929001215208

Classic LEDspotMV

Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001215208

Net weight (piece)	0.038 kg
--------------------	----------



Dimensional drawing




LEDClassic 50W GU10 WW 230V 36D ND 1BC/6

Product	D	C
Essential LED 4.6-50W GU10 827 36D	50 mm	54 mm

Photometric data





Essential Ledspot MV 50W 827 36D 1BC/6



Classic LEDspotMV

Lifetime



CLA LEDspotMV 50W GU10 827 36D ND

CLA LEDspotMV 50W GU10 827 36D ND

