



Classic LEDspotMV

Essential LED 4.6-50W GU10 827 36D

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimize maintenance costs.

Product data


General Information		Temperature	
Cap-Base	GU10 [GU10]	Lamp Current (Nom)	39 mA
EU RoHS compliant	Yes	Wattage Equivalent	50 W
Nominal Lifetime (Nom)	15000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.5 s
Technical Type	4.6-50W	Power Factor (Nom)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Color Code	827 [CCT of 2700K]	Dimmable	No
Beam Angle (Nom)	36°		
Luminous Flux (Nom)	395 lm	Approval and Application	
Luminous Intensity (Nom)	700 cd	Energy Efficiency Label (EEL)	A+
Color Designation	Warm White (WW)	Suitable For Accent Lighting	Yes
Correlated Color Temperature (Nom)	2700 K	Energy Consumption kWh/1000 h	5 kWh
Luminous Efficacy (rated) (Nom)	85.90 lm/W		
Color Consistency	<6	Product Data	
Color Rendering Index (Nom)	80	Full product code	871869670059400
LLMF At End Of Nominal Lifetime (Nom)	70 %	Order product name	Essential LED 4.6-50W GU10 827 36D
Operating and Electrical		EAN/UPC - Product	8718696700594
Input Frequency	50 to 60 Hz		
Power (Nom)	4.6 W		

Classic LEDspotMV

Order code	929001215208
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001215208

Net Weight (Piece)	0.038 kg
--------------------	----------



Dimensional drawing



LEDClassic 50W GU10 WW 230V 36D ND 1BC/6

Product	D	C
Essential LED 4.6-50W GU10 827 36D	50 mm	54 mm


Photometric data



Essential LedspotMV 51 1800lm 827 36D Page 10

LEDspotMV GU10 MR16 827

LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D




LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D

Classic LEDspotMV

Lifetime



CLA LEDspotMV 50W GU10 827 36D ND



CLA LEDspotMV 50W GU10 827 36D ND

