



# MASTER LEDspot MV

## MAS LEDspotMV VLE D 3.5-35W GU10 830 60D

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

### Product data

General Information	
Cap base	GU10 [ GU10]
Nominal lifetime (nom.)	35000 h
Switching cycle	50000X
Technical type	3.5-35W
Light Technical	
Colour code	830 [ CCT of 3,000 K]
Beam Angle (Nom)	60 °
Luminous flux (nom.)	315 lm
Luminous flux (rated) (nom.)	315 lm
Luminous intensity (nom.)	350 cd
Colour designation	White (WH)
Rated beam angle	60 °
Correlated colour temperature (nom.)	3000 K
Luminous efficacy (rated) (nom.)	90.00 lm/W
Colour consistency	<6

Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	275 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	3.5 W
Lamp current (nom.)	19 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C

# MASTER LEDspot MV

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application

Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

## Product Data


Full product code	871869656304500
-------------------	-----------------

Order product name	MAS LEDspotMV VLE D 3.5-35W GU10 830 60D
EAN/UPC – product	8718696563045
Order code	56304500
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001215902
Net weight (piece)	0.036 kg

## Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights



## Dimensional drawing



GU10 230V 4W-35W 260lm 60D 3000K GU10 D


Product	D	C
MAS LEDspotMV VLE D 3.5-35W GU10 830 60D	50 mm	56 mm

## Photometric data



# MASTER LEDspot MV

## Photometric data



Technical Parameters 41 Photo Lighting 8 11 Page 17

LED Lamps, CorePro LEDspotMV 3.5-35W GU10 PAR16 830 830 60D

