



# MASTER VALUE LEDspot MV

## MAS LEDspotMV VLE D 4.3-50W GU10 840 40D

Delivering a warm, halogen-like accent beam, MASTER VALUE is a perfect fit for spot lighting. Thanks to its high CRI, it realizes more natural colors, creating cozy and comfortable ambiances for residential and hospitality projects, and emphasizing the beauty of merchandise in retail. These LED spots MV GU10 have the familiar look and feel of spot lamps, keeping the classic beauty of glass spots and adding the strong performance of LED technology. The dimming function enables you to create the atmosphere you desire, and it works with broad selection of dimmers. MASTER VALUE also offers more energy savings than normal LED spots.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information			
Cap-Base	GU10 [GU10]	Luminous Intensity (Nom)	750 cd
Nominal lifetime	35,000 hour(s)	Color Designation	Cool White (CW)
Switching Cycle	50,000	Correlated Color Temperature (Nom)	4000 K
Lighting Technology	LED	Luminous Efficacy (rated) (Nom)	104.65 lm/W
EU RoHS compliant	Yes	Color Consistency	<6
		Color rendering index (CRI)	80
		LLMF At End Of Nominal Lifetime (Nom)	70 %
		Luminous Flux in 90° Cone (Rated)	390 lm
Light Technical		Operating and Electrical	
Color Code	840 [CCT of 4000K]	Line Frequency	50 to 60 Hz
Beam Angle (Nom)	40 degree(s)		
Luminous Flux	450 lm		

# MASTER VALUE LEDspot MV

Input Frequency	50 to 60 Hz
Power Consumption	4.3 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.8
Voltage (Nom)	220-240 V

## Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Bulb Shape	PAR16 [PAR 2 inch/50mm]
------------	-------------------------

## Approval and Application


Energy Saving Product	Yes
-----------------------	-----

Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	5 kWh

## Product Data



Order product name	MAS LEDspotMV VLE D 4.3-50W GU10 840 40D
Full product name	MAS LEDspotMV VLE D 4.3-50W GU10 840 40D
Full product code	871869656318200
Order code	929001216302
Material Nr. (12NC)	929001216302
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696563182
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696563199

## Dimensional drawing



Product	D	C
MAS LEDspotMV VLE D 4.3-50W GU10 840 40D	50 mm	56 mm

## Photometric data




Spectral Power Distribution Colour - MAS LEDspotMV VLE D 4.3-50W GU10 840 40D

Light Distribution Diagram - MAS LEDspotMV VLE D 4.3-50W GU10 840 40D

# MASTER VALUE LEDspot MV

## Photometric data



General uniform lighting - MAS LEDspotMV VLE D 4.3-50W GU10 840 40D

