



CorePro LEDspot MV

CorePro LEDspot 4-35W GU10 827 36D DIM

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. These GU10 LED spot lights are compatible with most existing fixtures with a GU10 LED base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots deliver significant energy savings and minimize maintenance costs.

Product data

General Information	
Cap-Base	GU10 [GU10]
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	36 degree(s)
Luminous Flux	250 lm
Luminous Intensity (Nom)	500 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	62.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux in 90° Cone (Rated)	250 lm
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	25 mA
Wattage Equivalent	35 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	65 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	PAR16 [PAR 2 inch/50mm]
Approval and Application	
Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	4 kWh

CorePro LEDspot MV

EyeComfort	Yes
Product Data	
Order product name	CorePro LEDspot 4-35W GU10 827 36D DIM
Full product name	CorePro LEDspot 4-35W GU10 827 36D DIM
Full product code	871869672133900
Order code	929001218632



Material Nr. (12NC)	929001218632
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696721339
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696721346

Dimensional drawing



Product	D	C
CorePro LEDspot 4-35W GU10 827 36D DIM	50 mm	53 mm

Photometric data



Light Distribution Diagram - CorePro LEDspot 4-35W GU10 827 36D DIM

General uniform lighting - CorePro LEDspot 4-35W GU10 827 36D DIM

Spectral Power Distribution Colour - CorePro LEDspot 4-35W GU10 827 36D
DIM

CorePro LEDspot MV

