



# Classic LEDspotMV

## CorePro LEDspot 5-50W GU10 827 36D DIM

Featuring a classic heritage design, Classic LEDspotMV delivers warm halogen-like light while saving around 90% on energy costs. It is compatible with most existing fixtures with a GU10 holder and is designed as a retrofit replacement for halogen or incandescent spots. LED lamps deliver significant energy savings and minimise maintenance costs.

#### **Product data**

General Information	
Cap base	GU10 [ GU10]
Nominal lifetime (nom.)	15000 h
Switching cycle	50000X
Technical type	5-50W
Light Technical	
Colour code	827 [ CCT of 2,700 K]
Beam Angle (Nom)	36 °
Luminous flux (nom.)	350 lm
Luminous intensity (nom.)	650 cd
Colour designation	Warm white (WW)
Correlated colour temperature (nom.)	2700 K
Luminous efficacy (rated) (nom.)	70.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous Flux in 90° Cone (Rated)	350 lm
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	5 W


Lamp current (nom.)	30 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	65 °C
Controls and Dimming	
Dimmable	Yes
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy Consumption kWh/1000 h	5 kWh
Product Data	
Full product code	871869672137700
Order product name	CorePro LEDspot 5-50W GU10 827 36D DIM
EAN/UPC – product	8718696721377

Datasheet, 2020, January 24 data subject to change

## Classic LEDspotMV

Order code	72137700
Numerator – quantity per pack	1
Numerator – packs per outer box	10
Material no. (12NC)	929001218832


#### Dimensional drawing




GU10 230V 5W-50W 385lm 60D 3000K GU10 ND


## Product D C CorePro LEDspot 5-50W GU10 827 36D DIM 50 mm 53 mm

#### Photometric data





LEDspotMV GU10 MR16 827



Calculat Procuments 43 Philips Lighting EV. Pages 37

LEDspotMV 5.5W-50W GU10 827 36D

## Classic LEDspotMV



© 2020 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.