



MASTER LEDtube InstantFit HF T8

MAS LEDtube HF 600mm 10.5W865 T8

Philips MASTER LEDtube InstantFit T8 integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. Philips MASTER LEDtube InstantFit T8 is the ideal solution for customers who have higher light requirements and want to maximize value over lifetime. Full energy savings & longer lifetime result in attractive payback times and TCO benefits.

Warnings and Safety

- NOTES: The overall energy efficiency and light distribution of any installation that uses these lamps are determined by the design of the installation.

Product data

General Information	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	1,050 lm
Correlated Color Temperature (Nom)	6500 K
Color Consistency	<6
Color rendering index (CRI)	83


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	20000-80000 Hz
Input Frequency	20000-80000 Hz
Power Consumption	10.5 W
Lamp Current (Max)	400 mA
Lamp Current (Min)	200 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	30-80 V

MASTER LEDtube InstantFit HF T8

Temperature	
T-Case Maximum (Nom)	40 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Product Length	600 mm
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	13 kWh


Product Data	
Order product name	MAS LEDtube HF 600mm 10.5W865 T8
Full product name	MAS LEDtube HF 600mm 10.5W865 T8
Full product code	871869655969700
Order code	929001219702
Material Nr. (12NC)	929001219702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696559697
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696559703

Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube HF 600mm 10.5W865 T8	25.6 mm	27.8 mm	588.6 mm	595.7 mm	602.8 mm

Photometric data




Light Distribution Diagram - MAS LEDtube HF 600mm 10.5W865 T8



Spectral Power Distribution Colour - MAS LEDtube HF 600mm 10.5W865 T8

MASTER LEDtube InstantFit HF T8

Photometric data



General uniform lighting – MAS LEDtube HF 600mm 10.5W865 T8

