



CorePro LEDtube EM/ Mains

CorePro LEDtube 1500mm 20W 865 C G

The CorePro LEDtube is an affordable LED solution suitable for replacing T8 fluorescent lamps. The product provides a natural lighting effect for use in general lighting applications, as well as instant energy savings – an environmentally friendly solution.

Product data

General Information		Power (Rated) (Nom)	
Cap base	G13 [Medium Bi-Pin Fluorescent]		20 W
Main application	Industrial	Lamp current (max.)	92 mA
Nominal lifetime (nom.)	30000 h	Lamp current (min.)	81 mA
Switching cycle	200000X	Starting time (nom.)	0.5 s
B50L70	30000 h	Warm-up time to 60% light (nom.)	instant full light s
Light Technical		Power factor (nom.)	0.9
Colour code	865 [CCT of 6,500 K]	Voltage (Nom)	220–240 V
Beam Angle (Nom)	240 °	Temperature	
Luminous flux (nom.)	2000 lm	T ambient (max.)	45 °C
Luminous flux (rated) (nom.)	2000 lm	T ambient (min.)	-20 °C
Rated beam angle	240 °	T storage (max.)	65 °C
Correlated colour temperature (nom.)	6500 K	T storage (min.)	-40 °C
Colour consistency	<6	T-Case maximum (nom.)	65 °C
Color rendering index (nom.)	80	Controls and Dimming	
LLMF at end of nominal lifetime (nom.)	70 %	Dimmable	No
Operating and Electrical			
Input frequency	50 to 60 Hz		

CorePro LEDtube EM/Mains

Mechanical and Housing

Product length 1500 mm

Approval and Application

Energy efficiency label (EEL) A+
 Energy-saving product Yes
 Suitable for accent lighting No
 Approval marks CE marking RoHS compliance KEMA Keur certificate
 Energy Consumption kWh/1000 h 20 kWh


Product Data

Full product code 871869656610700
 Order product name CorePro LEDtube 1500mm 20W 865 C G
 EAN/UPC – product 8718696566107
 Order code 56610700
 Numerator – quantity per pack 1
 Numerator – packs per outer box 10
 Material no. (I2NC) 929001221502
 Net weight (piece) 0.275 kg

Warnings and Safety

· -



Dimensional drawing



TLED 5ft 220-240V 20W-58W 6500K G13 ND

Product	D1	D2	A1	A2	A3
CorePro LEDtube 1500mm 20W 865 C G	25.7 mm	28 mm	1500 mm	1507.1 mm	1514.2 mm

Photometric data



CorePro LEDtube 1500mm 20W G13 865

CorePro LEDtube EM/Mains

Photometric data

