



# Classic filament LEDbulbs

## LEDClassic 4.5-50W P45 E27 WW CL D APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data


<b>General Information</b>		<b>Lamp Current (Nom)</b>		29 mA
Cap-Base	E27 [E27]	<b>Wattage Equivalent</b>		50 W
Nominal lifetime	15,000 hour(s)	<b>Starting Time (Nom)</b>		0.5 s
Switching Cycle	20,000	<b>Warm-up time to 60% light</b>		0.5 s
Rated Lifetime (Hours)	15 hour(s)	<b>Power Factor (Fraction)</b>		0.7
Lighting Technology	LED	<b>Voltage (Nom)</b>		220-240 V
EU RoHS compliant	Yes			
<b>Light Technical</b>		<b>Temperature</b>		
Color Code	827 [CCT of 2700K]	<b>T-Case Maximum (Nom)</b>		70 °C
Luminous Flux	470 lm	<b>Controls and Dimming</b>		
Color Designation	Warm White (WW)	<b>Dimmable</b>		Yes
Correlated Color Temperature (Nom)	2700 K	<b>Mechanical and Housing</b>		
Luminous Efficacy (rated) (Nom)	104.00 lm/W	<b>Bulb Finish</b>		Clear
Color Consistency	<6	<b>Bulb Shape</b>		P45 [P 45mm]
Color rendering index (CRI)	80	<b>Approval and Application</b>		
LLMF At End Of Nominal Lifetime (Nom)	70 %	<b>Energy Consumption kWh/1000 h</b>		5 kWh
<b>Operating and Electrical</b>		<b>Product Data</b>		
Line Frequency	50 to 60 Hz	<b>Order product name</b>		LEDClassic 4.5-50W P45 E27 WW CL D APR
Input Frequency	50 to 60 Hz			
Power Consumption	4.5 W			

## Classic filament LEDbulbs

Full product name	LEDClassic 4.5-50W P45 E27 WW CL D APR
Full product code	871869657481200
Order code	57481200
Material Nr. (12NC)	929001227608
Numerator - Quantity Per Pack	1


EAN/UPC - Product/Case	8718696574812
Numerator - Packs per outer box	10
EAN/UPC - Case	8718696574829

## Dimensional drawing




Product	D	C
LEDClassic 4.5-50W P45 E27 WW CL D APR	45 mm	89 mm


### Photometric data



**Spectral Power Distribution Colour - LEDClassic 4.5-50W P45 E27 WW CL D**  
**APR**



General uniform lighting - LEDClassic 4.5-50W P45 E27 WW CL D APR



Light Distribution Diagram - LEDClassic 4.5-50W P45 E27 WW CL D APR

## Classic filament LEDbulbs

