



Classic filament LEDbulbs

LEDClassic 4.5-50W P45 E27 WW CL D APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data


General Information		Lamp current (nom.)	
Cap base	E27 [E27]		29 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	50 W
Switching cycle	20000X	Starting time (nom.)	0.5 s
Technical type	4.5-50W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Controls and Dimming	
Colour Code	827 [CCT of 2,700 K]	Dimmable	Yes
Lamp Luminous Flux 25°C EL (Nom)	470 lm		
Lamp Luminous Flux (Nom)	470 lm	Mechanical and Housing	
Colour Designation	Warm white (WW)	Bulb finish	Clear (CL)
Colour Temperature, horizontal (Nom)	2700 K		
Lamp Luminous Efficacy EM (Nom)	104.00 lm/W	Approval and Application	
Colour consistency	<6	Energy efficiency label (EEL)	A++
Colour Rendering Index,horiz (Nom)	80	Energy Consumption kWh/1000 h	5 kWh
LLMF at end of nominal lifetime (nom.)	70 %		
Operating and Electrical		Product Data	
Input frequency	50 to 60 Hz	Full product code	871869657481200
Power (Rated) (Nom)	4.5 W	Order product name	LEDClassic 4.5-50W P45 E27 WW CL D APR

Classic filament LEDbulbs

EAN/UPC – product	8718696574812
Order code	929001227608
Numerator – quantity per pack	1
Numerator – packs per outer box	10

Material no. (12NC)	929001227608
Net weight (piece)	0.024 kg


Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27D

Product	D	C
LEDClassic 4.5-50W P45 E27 WW CL D APR	45 mm	89 mm


Photometric data



LED Lamps, Lightcolour /827 D CL



Classic LEDCandle D 4.5-40W P45 827 CL



Classic LEDCandle D 4.5-40W P45 827 CL

Classic filament LEDbulbs

