

Classic filament LEDbulbs

LEDClA 7.5-60W A60 E27 2000K GOLD APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

| General Information | |
|--|-----------------------|
| Cap base | E27 [E27] |
| Nominal lifetime (nom.) | 15000 h |
| Switching cycle | 20000X |
| Technical type | 7.5-60W |
| Light Technical | |
| Colour Code | 820 [CCT of 2,000 K] |
| Lamp Luminous Flux 25°C EL (Nom) | 600 lm |
| Lamp Luminous Flux (Nom) | 600 lm |
| Colour Designation | Flame |
| Colour Temperature, horizontal (Nom) | 2000 K |
| Lamp Luminous Efficacy EM (Nom) | 80.00 lm/W |
| Colour consistency | <6 |
| Colour Rendering Index,horiz (Nom) | 80 |
| LLMF at end of nominal lifetime (nom.) | 70 % |
| Operating and Electrical | |
| Input frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 7.5 W |

| Lamp current (nom.) | 42 mA |
|----------------------------------|--------------------|
| Wattage equivalent | 60 W |
| Starting time (nom.) | 0.5 s |
| Warm-up time to 60% light (nom.) | 0.5 s |
| Power factor (nom.) | 0.7 |
| Voltage (Nom) | 220-240 V |
| Controls and Dimming | |
| Dimmable | Yes |
| Mechanical and Housing | |
| Bulb finish | Gold-Clear (GO-CL) |
| Approval and Application | |
| Energy efficiency label (EEL) | A+ |
| Energy-saving product | Yes |
| Suitable for accent lighting | No |
| Energy Consumption kWh/1000 h | 8 kWh |


Classic filament LEDbulbs

Product Data

| | |
|-------------------------------|---------------------------------------|
| Full product code | 871869657483600 |
| Order product name | LEDClA 7.5-60W A60 E27 2000K GOLD APR |
| EAN/UPC – product | 8718696574836 |
| Order code | 929001228108 |
| Numerator – quantity per pack | 1 |

| | |
|---------------------------------|--------------|
| Numerator – packs per outer box | 12 |
| Material no. (12NC) | 929001228108 |
| Net weight (piece) | 0.030 kg |


Dimensional drawing




filament 7W-60W 620lm NAD 2200K E27D

| Product | D | C |
|---------------------------------------|-------|--------|
| LEDClA 7.5-60W A60 E27 2000K GOLD APR | 60 mm | 112 mm |


Photometric data



LED Lamps, Lightcolour /820 ST64 GOLD



Classic LEDBulb D 7.5-48W A60 820 GOLD



Classic LEDBulb D 7.5-48W A60 820 GOLD

Classic filament LEDbulbs

