

Classic filament LEDbulbs

LEDClA 7.5-60W A60 E27 2000K GOLD APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7.5-60W
Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux (Nom)	600 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	80.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	7.5 W

Lamp Current (Nom)	42 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Gold Clear
Approval and Application	
Energy Efficiency Label (EEL)	A+
Energy Saving Product	Yes
Suitable For Accent Lighting	No

Classic filament LEDbulbs

Energy Consumption kWh/1000 h	8 kWh
Product Data	
Full product code	871869657483600
Order product name	LEDClA 7.5-60W A60 E27 2000K GOLD APR
EAN/UPC - Product	8718696574836
Order code	929001228108

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	929001228108
Net Weight (Piece)	0.030 kg



Dimensional drawing




Product	D	C
LEDClA 7.5-60W A60 E27 2000K GOLD APR	60 mm	112 mm

filament 7W-60W 620lm NAD 2200K E27D

Photometric data



LED Lamps, Lightcolour /820 ST64 GOLD



Classic LEDBulb D 7.5-48W A60 820 GOLD

Classic LEDBulb D 7.5-48W A60 820 GOLD

Classic filament LEDbulbs

