

Decorative LED bulbs

CLA LEDBulb D 7-50W ST64 B22 820 GOLD

The new Deco collection transforms your home with a perfect blend of warm white light and a lean, minimalistic lighting experience. With long lifetime, up to 90% energy savings, no flickering and an instant full-level brightness, you will also enjoy soft and evenly distributed light with that trendy and stylish charm for a welcoming harmony in your space.

Product data

General Information	
Cap base	B22 [B22]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	7-50W

Light Technical	
Colour code	820 [CCT of 2,000 K]
Luminous flux (nom.)	630 lm
Luminous flux (rated) (nom.)	630 lm
Colour designation	Flame
Correlated colour temperature (nom.)	2000 K
Luminous efficacy (rated) (nom.)	90.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7 W
Lamp current (nom.)	40 mA
Wattage equivalent	50 W

Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V

Controls and Dimming	
Dimmable	Yes


Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	7 kWh

Product Data	
Full product code	871869658107000
Order product name	CLA LEDBulb D 7-50W ST64 B22 820 GOLD
EAN/UPC – product	8718696581070
Order code	58107000
Numerator – quantity per pack	1
Numerator – packs per outer box	6
Material no. (12NC)	929001228402

Decorative LED bulbs

Net weight (piece) 0.060 kg



Dimensional drawing




filament 7W-60W 620lm NAD 2200K E27D

Product	D	C
CLA LEDBulb D 7-50W ST64 B22 820 GOLD	64 mm	146.5 mm

Photometric data



Classic LEDBulb D 7-50W ST64 820 GOLD



Decorative LED bulbs

