



Classic filament LEDbulbs

LEDClassic 8-70W ST64 E27 WW CL D APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes

Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	115.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7 W

Lamp Current (Nom)	40 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V

Temperature	
T-Case Maximum (Nom)	70 °C

Controls and Dimming	
Dimmable	Yes

Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	ST64


Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	7 kWh

Classic filament LEDbulbs

Product Data	
Order product name	LEDClassic 7-70W ST64 E27 WW CL D APR
Full product name	LEDClassic 8-70W ST64 E27 WW CL D APR
Full product code	871869657487400
Order code	57487400
Material Nr. (12NC)	929001228608

Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574874
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574881

Dimensional drawing



Product	D	C
LEDClassic 7-70W ST64 E27 WW CL D APR	64 mm	148 mm

Photometric data




Spectral Power Distribution Colour - LEDClassic 7-70W ST64 E27 WW CL D APR

General Uniform Lighting

Candle 7.0w 2700K B21ST64 9290012288
7 x 965 lm

CalcLux Parameters 4.3 Philips Lighting B.V. Page 1/1

General uniform lighting - LEDClassic 7-70W ST64 E27 WW CL D APR



Light Distribution Diagram - LEDClassic 7-70W ST64 E27 WW CL D APR

Classic filament LEDbulbs

