



# Classic filament LEDbulbs

## LEDClassic 7-70W ST64 E27 WW CL D APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General information	
Cap-Base	E27 [ E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	7-70W
Light technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	115.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	7 W


Lamp Current (Nom)	40 mA
Wattage Equivalent	70 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and dimming	
Dimmable	Yes
Mechanical and housing	
Bulb Finish	Clear
Bulb Shape	ST64
Approval and application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No

# Classic filament LEDbulbs

Energy Consumption kWh/1000 h	7 kWh
<b>Product data</b>	
Full product code	871869657487400
Order product name	LEDClassic 7-70W ST64 E27 WW CL D APR
EAN/UPC - Product	8718696574874
Order code	929001228608

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material Nr. (12NC)	929001228608
Net Weight (Piece)	0.060 kg


## Dimensional drawing




LEDClassic 7-70W ST64 E27 WW CL D APR

Product	D	C
LEDClassic 7-70W ST64 E27 WW CL D APR	64 mm	148 mm


## Photometric data



LED Lamps, Lightcolour /827 ST64 GOLD



Classic LEDBulb D 7-60W ST64 827 CL



Classic LEDBulb D 7-60W ST64 827 CL

## Classic filament LEDbulbs

