

# Premium LED bulbs

## Vintage Filament

### LEDClassic 50W ST64 E27 2000K GOLD D SRT

Featuring a classic heritage design, the new Philips Vintage LED lamp family is reminiscent of familiar incandescent bulbs. Available in an array of giant shapes, candles and other familiar form factors, they provide a seamless fit across your space. When used as a statement piece, they add a sense of nostalgia and create a highly desirable atmosphere for socialization and relaxing.

#### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux	630 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	ST64
Approval and Application	
Energy Consumption kWh/1000 h	7 kWh

Premium LED bulbs Vintage Filament

EyeComfort	Yes
Product Data	
Order product name	LEDClassic 50W ST64 E27 2000K GOLD D SRT
Full product name	LEDClassic 50W ST64 E27 2000K GOLD D SRT
Full product code	871869657539002
Order code	929001228958



Material Nr. (12NC)	929001228958
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696575390
Numerator - Packs per outer box	4
EAN/UPC - Case	8718696751039

Dimensional drawing



Product	D	C
LEDClassic 50W ST64 E27 2000K GOLD D SRT	64 mm	148 mm

Photometric data



Spectral Power Distribution Colour - LEDClassic 50W ST64 E27 2000K GOLD D SRT

General uniform lighting - LEDClassic 50W ST64 E27 2000K GOLD D SRT

