



Classic filament LEDbulbs

LEDClassic 7-60W G120 E27 2000K GOLD APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime (nom.)	15000 h
Switching cycle	20000X
Technical type	7-60W
Light Technical	
Colour Code	820 [CCT of 2,000 K]
Lamp Luminous Flux 25°C EL (Nom)	630 lm
Lamp Luminous Flux (Nom)	630 lm
Colour Designation	Flame
Colour Temperature, horizontal (Nom)	2000 K
Lamp Luminous Efficacy EM (Nom)	90.00 lm/W
Colour consistency	<6
Colour Rendering Index,horiz (Nom)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	7 W

Lamp current (nom.)	40 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.7
Voltage (Nom)	220-240 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb finish	Gold-Clear (GO-CL)
Approval and Application	
Energy efficiency label (EEL)	A+
Energy-saving product	Yes
Suitable for accent lighting	No
Energy Consumption kWh/1000 h	7 kWh


Classic filament LEDbulbs

Product Data

Full product code	871869657493500
Order product name	LEDClassic 7-60W G120 E27 2000K GOLD APR
EAN/UPC – product	8718696574935
Order code	929001229108
Numerator – quantity per pack	1

Numerator – packs per outer box	6
Material no. (12NC)	929001229108
Net weight (piece)	0.115 kg


Dimensional drawing




filament 7W-60W 620lm NAD 2200K E27D

Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm


Photometric data



LED Lamps, Lightcolour /820 ST64 GOLD



Classic LEDBulb D 7-50W G120 820 GOLD



Classic LEDBulb D 7-50W G120 820 GOLD

Classic filament LEDbulbs

