



# Classic filament LEDbulbs

## LEDClassic 7-60W G120 E27 2000K GOLD APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

### Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	820 [CCT of 2000K]
Luminous Flux	630 lm
Color Designation	Flame
Correlated Color Temperature (Nom)	2000 K
Luminous Efficacy (rated) (Nom)	90.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz


Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Finish	Gold Clear
Bulb Shape	G120 [G 120mm]

Classic filament LEDbulbs

Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	7 kWh
Product Data	
Order product name	LEDClassic 7-60W G120 E27 2000K GOLD APR
Full product name	LEDClassic 7-60W G120 E27 2000K GOLD APR


Full product code	871869657493500
Order code	929001229108
Material Nr. (12NC)	929001229108
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574935
Numerator - Packs per outer box	6
EAN/UPC - Case	8718696574942

Dimensional drawing




Product	D	C
LEDClassic 7-60W G120 E27 2000K GOLD APR	125 mm	188 mm

Photometric data




Spectral Power Distribution Colour – LEDClassic 7-60W G120 E27 2000K GOLD APR



General uniform lighting – LEDClassic 7-60W G120 E27 2000K GOLD APR

## Classic filament LEDbulbs

### Photometric data



Light Distribution Diagram - LEDClassic 7-60W G120 E27 2000K GOLD APR

