



Standard LED bulbs

LEDGlobe8.5-60W G30 E27 CDL W ND MX

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information		Wattage Equivalent	
Cap-Base	E27 [E27]	60 W	
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	
Switching Cycle	50,000	0.5 s	
Lighting Technology	LED	Warm-up time to 60% light	
EU RoHS compliant	Yes	0.5 s	
Light Technical		Power Factor (Fraction)	
Color Code	865 [CCT of 6500K]	0.7	
Beam Angle (Nom)	150 degree(s)	Voltage (Nom)	
Luminous Flux	806 lm	100-240 V	
Color Designation	Cool Daylight	Temperature	
Correlated Color Temperature (Nom)	6500 K	T-Case Maximum (Nom)	
Luminous Efficacy (rated) (Nom)	94.00 lm/W	52 °C	
Color Consistency	<6	Controls and Dimming	
Color rendering index (CRI)	80	Dimmable	
LLMF At End Of Nominal Lifetime (Nom)	70 %	No	
Operating and Electrical		Mechanical and Housing	
Line Frequency	50 to 60 Hz	Bulb Finish	
Input Frequency	50 to 60 Hz	Frosted	
Power Consumption	8.5 W	Bulb Shape	
		G30	
		Approval and Application	
		Energy Consumption kWh/1000 h	
		9 kWh	
		Product Data	
		Order product name	
		LEDGlobe8.5-60W G30 E27 CDL W ND MX	
		Full product name	
		LEDGlobe8.5-60W G30 E27 CDL W ND MX	

Standard LED bulbs

Full product code	871869678888200
Order code	929001229371
Material Nr. (12NC)	929001229371
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696788882

Numerator - Packs per outer box	4
EAN/UPC - Case	8718696788899

Dimensional drawing



Product	D	C
LEDGlobe8.5-60W G30 E27 CDL W ND MX	95 mm	128 mm

