



Standard LED bulbs

Standard LEDBulb LEDGlobe8.5-60W G30 E27 CDL W ND MX

Standard LED bulbs are compatible with existing fixtures with a E27 holder and are designed for retrofit replacement of incandescent, halogen and energy saving bulbs. They deliver huge energy savings and minimize maintenance costs. The Standard LED bulb is the perfect bulb for your basic lighting needs. It provides the beautiful light and performance you expect from the LED technology at an affordable price.

Product data


General Information		Power (Rated) (Nom)	
Cap-Base	E27 [E27]	Power (Rated) (Nom)	8.5 W
RoHS mark	RoHS mark	Wattage Equivalent	60 W
Nominal Lifetime (Nom)	15000 h	Starting Time (Nom)	0.5 s
Switching Cycle	50000X	Warm Up Time to 60% Light (Nom)	0.5 s
Technical Type	8.5-60W	Power Factor (Nom)	0.7
		Lamp Current at 127V	80 mA
		Lamp Current at 220V	45 mA
		Voltage (Nom)	100-240 V
Light Technical		Temperature	
Color Code	865 [CCT of 6500K]	T-Case Maximum (Nom)	52 °C
Beam Angle (Nom)	150 °		
Luminous Flux (Nom)	806 lm	Controls and Dimming	
Luminous Flux (Rated) (Nom)	806 lm	Dimmable	No
Color Designation	Cool Daylight	Mechanical and Housing	
Correlated Color Temperature (Nom)	6500 K	Bulb Finish	Frosted
Luminous Efficacy (rated) (Nom)	94.00 lm/W	Approval and Application	
Color Consistency	<6	Energy Efficiency Label (EEL)	A+
Color Rendering Index (Nom)	80		
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical			
Input Frequency	50 to 60 Hz		

Standard LED bulbs

Energy Consumption kWh/1000 h	9 kWh
Product Data	
Full product code	871869678888200
Order product name	Standard LEDBulb LEDGlobe8.5-60W G30 E27 CDL W ND MX
EAN/UPC - Product	8718696788882

Order code	929001229371
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	4
Material Nr. (12NC)	929001229371
Net Weight (Piece)	0.125 kg

Dimensional drawing



Product	D	C
LEDGlobe8.5-60W G30 E27 CDL W ND MX	95 mm	128 mm

bulb 100-240V 10W-60W 806lm 6500K E27ND

