



CorePro LEDcapsule MV

CorePro LEDcapsuleMV 2.3-25W G9 827 D

This single-ended mains-voltage capsule for G9-base luminaires delivers directional light, making it a true alternative to halogen capsule lamps. It is particularly suitable for task lighting in shops, hotels and restaurants, and ideal for desk lamps and cabinet lighting. Compatible with existing fixtures with G9 holders and designed for retrofit replacement of halogen capsules, CorePro LEDcapsule delivers huge energy savings and minimizes maintenance costs, without any compromise on light quality.

Product data


General Information		Power (Rated) (Nom)	
Cap base	G9 [G9]		2.3 W
Nominal lifetime (nom.)	15000 h	Lamp current (nom.)	15 mA
Switching cycle	50000X	Wattage equivalent	25 W
Technical type	2.3-25W	Starting time (nom.)	0.5 s
		Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	827 [CCT of 2,700 K]	T-Case maximum (nom.)	82 °C
Lamp Luminous Flux 25°C EL (Nom)	215 lm		
Lamp Luminous Flux (Nom)	215 lm	Controls and Dimming	
Colour Designation	Warm white (WW)	Dimmable	Yes
Colour Temperature, horizontal (Nom)	2700 K		
Lamp Luminous Efficacy EM (Nom)	93.48 lm/W	Approval and Application	
Colour consistency	<6	Energy efficiency label (EEL)	A++
Colour Rendering Index,horiz (Nom)	80	Energy-saving product	Yes
LLMF at end of nominal lifetime (nom.)	70 %	Suitable for accent lighting	No
Operating and Electrical			
Input frequency	50 to 60 Hz		

CorePro LEDcapsule MV

Energy Consumption kWh/1000 h	3 kWh
Product Data	
Full product code	871869657869800
Order product name	CorePro LEDcapsuleMV 2.3-25W G9 827 D
EAN/UPC – product	8718696578698
Order code	57869800

Numerator – quantity per pack	1
Numerator – packs per outer box	12
Material no. (12NC)	929001232002
Net weight (piece)	0.012 kg


Dimensional drawing




Capsule 230V 2.3W-25W 210lm 2700K G9 D

Product	D	C
CorePro LEDcapsuleMV 2.3-25W G9 827 D	23 mm	51 mm


Photometric data



LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827



LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827



LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827

CorePro LEDcapsule MV

