



CorePro LEDcapsuleMV

CorePro LEDcapsuleMV 2.3-25W G9 827 D

The LED specialties deliver a high quality light to make themselves to be a true replacement of halogen specialty lamp (such as G9 and R7S). It is particularly suit for task lighting in hotel and restaurants, and ideal for decorative and ambient application. LEDspecialty products deliver huge energy saving and minimize maintenance costs, without any compromise on light quality.

Product data


General Information		Power Consumption	
Cap-Base	G9 [G9]	Lamp Current (Nom)	2.3 W
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	15 mA
Switching Cycle	50,000	Starting Time (Nom)	25 W
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
EU RoHS compliant	Yes	Power Factor (Fraction)	0.5 s
Light Technical		Voltage (Nom)	0.7
Color Code	827 [CCT of 2700K]	Temperature	
Luminous Flux	215 lm	T-Case Maximum (Nom)	82 °C
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	Yes
Luminous Efficacy (rated) (Nom)	93.48 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Shape	Capsule
Color rendering index (CRI)	80	Approval and Application	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Energy Saving Product	No
Operating and Electrical		Suitable For Accent Lighting	No
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

CorePro LEDcapsule MV

Energy Consumption kWh/1000 h	3 kWh
Product Data	
Order product name	CorePro LEDcapsuleMV 2.3-25W G9 827 D
Full product name	CorePro LEDcapsuleMV 2.3-25W G9 827 D
Full product code	871869657869800
Order code	929001232002


Material Nr. (12NC)	929001232002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696578698
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696578704

Dimensional drawing




Product	D	C
CorePro LEDcapsuleMV 2.3-25W G9 827 D	23 mm	51 mm


Photometric data



Spectral Power Distribution Colour - CorePro LEDcapsuleMV 2.3-25W G9
827 D



General uniform lighting - CorePro LEDcapsuleMV 2.3-25W G9 827 D



Light Distribution Diagram - CorePro LEDcapsuleMV 2.3-25W G9 827 D

CorePro LEDcapsule MV

