



# CorePro LEDcapsule MV

## CorePro LEDcapsuleMV 2.3-25W G9 827 D

The LED specialties deliver a high quality light to make themselves to be a true replacement of halogen specialty lamp (such as G9 and R7S). It is particularly suit for task lighting in hotel and restaurants, and ideal for decorative and ambient application. LEDspecialty products deliver huge energy saving and minimize maintenance costs, without any compromise on light quality.

### Product data

General Information	
Cap-Base	G9 [ G9]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	50000X
Technical Type	2.3-25W
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	215 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	93.48 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	2.3 W

Lamp Current (Nom)	15 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	82 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb Shape	Capsule
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No

# CorePro LEDcapsule MV

Energy Consumption kWh/1000 h	3 kWh
<b>Product Data</b>	
Full product code	871869657869800
Order product name	CorePro LEDcapsuleMV 2.3-25W G9 827 D
EAN/UPC - Product	8718696578698
Order code	929001232002

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	929001232002
Net Weight (Piece)	0.012 kg



## Dimensional drawing

D

Product	D	C
CorePro LEDcapsuleMV 2.3-25W G9 827 D	23 mm	51 mm


Capsule 230V 2.3W-25W 210lm 2700K G9 D

## Photometric data



LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827

LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827



LED Lamps, CorePro LEDcapsuleMV D 2.3-25W G9 /827

## CorePro LEDcapsule MV

