



# CorePro LEDspot Reflectors

## CorePro LEDspotMV ND 2.7-40W 827 R63 36D

CorePro LEDspots Reflectors are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with an E27 or E14 base and are designed as a retrofit replacement for halogen or incandescent spots. CorePro LEDspots Reflectors deliver significant energy savings and minimise maintenance costs.

### Product data

General Information	
Cap base	E27 [E27]
Nominal lifetime	15,000 h
Switching Cycle	50,000
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Colour Code	827 [CCT of 2700K]
Beam angle (nom.)	36 degree(s)
Luminous Flux	210 lm
Luminous intensity (nom.)	450 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature	2700 K
Luminous efficacy (rated) (nom.)	77.78 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	210 lm


Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	2.7 W
Lamp current (nom.)	25 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	1 s
Power Factor (Fraction)	0.4
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	82 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb shape	R63 [R 63 mm]

CorePro LEDspot Reflectors

Approval and Application	
Energy-saving product	Yes
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	3 kWh
Product Data	
Order product name	CorePro LEDspotMV ND 2.7-40W 827 R63 36D
Full product name	CorePro LEDspotMV ND 2.7-40W 827 R63 36D
Full EOC	871869657859900


Order code	57859900
Material no. (12 NC)	929001233602
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8718696578599
Numerator – packs per outer box	6
EAN/UPC – Case	8718696578605

Dimensional drawing




Product	D	C
CorePro LEDspotMV ND 2.7-40W 827 R63 36D	63 mm	102 mm


Photometric data



Spectral Power Distribution Colour - CorePro LEDspotMV ND 2.7-40W 827 R63 36D



General uniform lighting - CorePro LEDspotMV ND 2.7-40W 827 R63 36D



Light Distribution Diagram - CorePro LEDspotMV ND 2.7-40W 827 R63 36D

## CorePro LEDspot Reflectors

