

Classic filament LEDbulbs

CLA LEDBulb ND 4-40W A60 E27 827 CL

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

| General Information | |
|-------------------------|------------|
| Cap base | E27 [E27] |
| Nominal lifetime (nom.) | 15000 h |
| Switching cycle | 20000X |
| Technical type | 4-40W |

| Light Technical | |
|--|-----------------------|
| Colour code | 827 [CCT of 2,700 K] |
| Luminous flux (nom.) | 470 lm |
| Luminous flux (rated) (nom.) | 470 lm |
| Colour designation | Warm White (WW) |
| Correlated colour temperature (nom.) | 2700 K |
| Luminous efficacy (rated) (nom.) | 117.50 lm/W |
| Colour consistency | <6 |
| Color rendering index (nom.) | 80 |
| LLMF at end of nominal lifetime (nom.) | 70 % |

| Operating and Electrical | |
|--------------------------|-------------|
| Input frequency | 50 to 60 Hz |
| Power (Rated) (Nom) | 4 W |
| Lamp current (nom.) | 33 mA |
| Wattage equivalent | 40 W |

| | |
|----------------------------------|-----------|
| Starting time (nom.) | 0.5 s |
| Warm-up time to 60% light (nom.) | 0.5 s |
| Power factor (nom.) | 0.4 |
| Voltage (Nom) | 220-240 V |

| Controls and Dimming | |
|----------------------|----|
| Dimmable | No |

| Mechanical and Housing | |
|------------------------|------------|
| Bulb finish | Clear (CL) |

| Approval and Application | |
|-------------------------------|-------|
| Energy efficiency label (EEL) | A++ |
| Energy-saving product | Yes |
| Suitable for accent lighting | No |
| Energy Consumption kWh/1000 h | 4 kWh |


| Product Data | |
|--------------------|-------------------------------------|
| Full product code | 871869657399000 |
| Order product name | CLA LEDBulb ND 4-40W A60 E27 827 CL |
| EAN/UPC – product | 8718696573990 |
| Order code | 57399000 |

Classic filament LEDbulbs

| | |
|---------------------------------|--------------|
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 10 |
| Material no. (12NC) | 929001237102 |

| | |
|--------------------|----------|
| Net weight (piece) | 0.030 kg |
|--------------------|----------|



Dimensional drawing




filament 4.5W-40W 470lm NAD 2700K E27ND

| Product | D | C |
|-------------------------------------|-------|--------|
| CLA LEDBulb ND 4-40W A60 E27 827 CL | 60 mm | 104 mm |

Photometric data



CorePro LEDbulb ND 4-40W A60 827



Classic filament LEDbulbs

