

Classic filament LEDbulbs

LEDClassic 4-50W A60 E27 WW CL ND APR

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	118.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W


Lamp Current (Nom)	33 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Shape	A60 [A 60mm]
Approval and Application	
Energy Saving Product	Yes
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	4 kWh

Classic filament LEDbulbs

Product Data	
Order product name	LEDClassic 4-50W A60 E27 WW CL ND APR
Full product name	LEDClassic 4-50W A60 E27 WW CL ND APR
Full product code	871869657419500
Order code	929001237108
Material Nr. (12NC)	929001237108


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574195
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696574201

Dimensional drawing




Product	D	C
LEDClassic 4-50W A60 E27 WW CL ND APR	60 mm	104 mm


Photometric data



Spectral Power Distribution Colour - LEDClassic 4-50W A60 E27 WW CL ND APR



General uniform lighting - LEDClassic 4-50W A60 E27 WW CL ND APR



Light Distribution Diagram - LEDClassic 4-50W A60 E27 WW CL ND APR

Classic filament LEDbulbs

