

Classic filament LED Lamps

LEDClassic 4-50W A60 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LED bulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information		Lamp current (nom.)	
Cap base	E27 [E27]		33 mA
Nominal lifetime (nom.)	15000 h	Wattage equivalent	50 W
Switching cycle	20000X	Starting time (nom.)	0.5 s
Technical type	4-50W	Warm-up time to 60% light (nom.)	0.5 s
		Power factor (nom.)	0.4
		Voltage (nom.)	220-240 V
Light Technical		Controls and Dimming	
Colour Code	827 [CCT of 2700K]	Dimmable	No
Lamp Luminous Flux 25°C EL (Nom)	470 lm		
Lamp Luminous Flux (Nom)	470 lm	Mechanical and Housing	
Colour Designation	Warm white (WW)	Bulb finish	Clear
Colour Temperature, horizontal (Nom)	2700 K		
Lamp Luminous Efficacy EM (Nom)	118.00 lm/W	Approval and Application	
Colour consistency	<6	Energy-saving product	Yes
Colour Rendering Index,horiz (Nom)	80	Suitable for accent lighting	No
LLMF at end of nominal lifetime (nom.)	70 %	Energy efficiency label (EEL)	A++
		Energy Consumption kWh/1000 h	4 kWh
Operating and Electrical			
Input frequency	50 to 60 Hz		
Technical Lamp Power (Nom)	4 W		


Classic filament LED Lamps

Product Data

Full product code	871869657419500
Order product name	LEDClassic 4-50W A60 E27 WW CL ND APR
EAN/UPC – product	8718696574195
Order code	929001237108
Numerator – quantity per pack	1

Numerator – packs per outer box	12
Material no. (12NC)	929001237108
Net weight (piece)	0.030 kg




Dimensional drawing



filament 4.5W-40W 470lm NAD 2700K E27ND

Product	D	C
LEDClassic 4-50W A60 E27 WW CL ND APR	60 mm	104 mm

Photometric data



Classic filament LED Lamps

