

Classic filament LEDbulbs

LEDClassic 4-50W A60 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	4-50W
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux (Nom)	470 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	118.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	4 W

Lamp Current (Nom)	33 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	70 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Saving Product	Yes
Suitable For Accent Lighting	No

Classic filament LEDbulbs

Energy Consumption kWh/1000 h	4 kWh
Product Data	
Full product code	871869657419500
Order product name	LEDClassic 4-50W A60 E27 WW CL ND APR
EAN/UPC - Product	8718696574195
Order code	929001237108

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	929001237108
Net Weight (Piece)	0.030 kg



Dimensional drawing



Product	D	C
LEDClassic 4-50W A60 E27 WW CL ND APR	60 mm	104 mm


filament 4.5W-40W 470lm NAD 2700K E27ND

Photometric data



LED Lamps, Lightcolour /827 ND CL

CorePro LEDbulb ND 4-40W A60 827



CorePro LEDbulb ND 4-40W A60 827

Classic filament LEDbulbs

