



# Classic filament LEDbulbs

## LEDClassic 6-70W A60 E27 WW CL ND APR

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.


### Product data

General Information			
Cap-Base	E27 [E27]	Power Consumption	6 W
Nominal lifetime	15000 hour(s)	Lamp Current (Nom)	52 mA
Switching Cycle	20000	Wattage Equivalent	70 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
EU RoHS compliant	Yes	Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.5
		Voltage (Nom)	220-240 V
Light Technical			
Color Code	827 [CCT of 2700K]	Controls and Dimming	
Luminous Flux	806 lm	Dimmable	No
Color Designation	Warm White (WW)	Mechanical and Housing	
Correlated Color Temperature (Nom)	2700 K	Bulb Finish	Clear
Luminous Efficacy (rated) (Nom)	134.00 lm/W	Bulb Shape	A60 [A 60mm]
Color Consistency	<lt/>6	Approval and Application	
Color rendering index (CRI)	80	Energy Saving Product	Yes
LLMF At End Of Nominal Lifetime (Nom)	70 %	Suitable For Accent Lighting	No
Operating and Electrical		Energy Consumption kWh/1000 h	6 kWh
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz		

Classic filament LEDbulbs

Product Data	
Order product name	LEDClassic 6-70W A60 E27 WW CL ND APR
Full product name	LEDClassic 6-70W A60 E27 WW CL ND APR
Full product code	871869657421800
Order code	929001237208
Material Nr. (12NC)	929001237208


Dimensional drawing




Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696574218
Numerator - Packs per outer box	12
EAN/UPC - Case	8718696574225

Product	D	C
LEDClassic 6-70W A60 E27 WW CL ND APR	60 mm	104 mm

Photometric data



Spectral Power Distribution Colour - LEDClassic 6-70W A60 E27 WW CL ND APR



Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram - LEDClassic 6-70W A60 E27 WW CL ND APR



Lumen Maintenance Diagram - LEDClassic 6-70W A60 E27 WW CL ND APR

